

MR-E Super

Servo and Motion Control

**Excellent performance, small price
and easy operation**



Wide output range (100 W – 2 kW) for any kind of application



High accuracy positioning thanks to the integrated high resolution encoder (131072 pls/rev)



High-speed pulse train interface (1 MHz) for more precise command handling



Auto-tuning and diagnostic tools for easy and time-saving installation

User-friendly servo with easy operation



Bottle filling machines with Mitsubishi MR-E servo systems cut down system cost

With the MR-E Super, Mitsubishi Electric launches a servo drive on the market with unique functions and very compact dimensions. It was developed with great attention to a very quick and easy commissioning.

Thanks to its high positioning accuracy and responsiveness, the MR-E Super is an excellent choice for applications ranging from 100 W to 2 kW.



Filling, processing and packaging in the food industry is one of the applications where MR-E Super can be found

The MR-E Super is available with pulse-train input for position and internal speed control or analog input for speed and torque control. The amplifier features Mitsubishi Electric's legendary auto-tuning and vibration suppression functions. Set-up and diagnosis is easy with the Windows based software MR-Configurator.

Compared to its performance the MR-E Super is a well-priced product for very cost-effective and economical servo solutions.

Full range for all applications

The Mitsubishi general-purpose AC servo system MR-E Super can perform operation in different control modes, e.g. position/internal speed control. Hence, it fits a wide range of applications such as precision positioning and smooth speed control of machine tools and general industrial machines (e.g. packaging, processing or labelling machines).

■ Position/internal speed control mode

Up to 1 Mpps high-speed pulse train is used to control the speed and direction of the motor and execute precision positioning also taking advantage of the high encoder revolution of 131072 pulses/rev.

With the position smoothing function a smoother start/stop can be made in response to a sudden position command. If the application demands to control smoothly the speed of the motor, the MR-E Super also offers the possibility to switch "on-the-fly" to the internal speed modality. In this way it is possible to address up to 7 different parameter-driven speeds using 3 digital inputs.

■ Speed/torque control mode

External analog speed command (0 to ± 10 V) or torque command (0 to ± 8 V) are implemented making this new servo system suitable for those applications in which speed or torque has to be smoothly controlled.

High precision positioning – high flexibility

For the MR-E Super series a wide range of motor sizes from low to medium inertia are available. Hence this new servo can be considered as a powerful system for any general-purpose application, but at the same time, a cost-effective solution for the replacement of stepping motors or DC servos.

All MR-E Super servo motors are equipped with an incremental position encoder and offer a high level of internal protection.



HF-SE and HF-KE servo motors

Latest technology – easy to use

All MR-E Super servo amplifiers use the latest regulation and control technologies. These systems ensure fast installation and setup, and make it possible to configure stable systems with very short response times – no matter what application.

Real-time auto-tuning

The well-known real-time auto-tuning function from Mitsubishi Electric sets the servo's control parameters automatically, eliminating the need to calibrate the system for each individual application. But that's not all – auto-tuning also works continuously while the system is in operation, making constant adjustments to cater for applications with fluctuating moments of inertia. This makes it possible to use MR-E Super in a much wider range of applications.

High-speed response

Increased dynamics and more precise positioning can be handled thanks to the high response frequency of 500 Hz.

Advanced suppression of mechanical vibration

The MR-E Super has an automatic feature that enables the amplifier to minimize the effects of a vibrating load. For example, this innovative function can also suppress vibrations at the end of a tool arm as well as those in the drive train.

Advanced features


Quick and easy wiring

Connectors have been adapted for the servo amplifier terminal block and all connectors are located on the front of the servo amplifier which makes wiring fast and easy.

Auxiliary equipment

EMC footprint filters are available in order to comply with the EMC Directive of the EN Standard.

The specific terminal block can also be used in order to make the I/O wiring easier.




More precise positioning can be handled with the high-speed input interface

Compact component size

The compact component size is critically important to machine designers who are often called upon to squeeze all of the control solutions they need into the smallest deliverable package. This means machine designers don't have to make as many compromises to get the right motor and deliver the right power to the right place. The compact dimensions of the MR-E Super series enable flexible installation and economical design, which helps to keep the costs down and to be more competitive on the global market.

User-friendly software



Monitoring and checking with the diagnostic tools

The MR Configurator software package makes tuning and diagnostics quick and easy and includes powerful graphical machine analysis and simulation functions. A machine analyzer allows you to get the frequency response of the connected mechanical system without any additional instruments. If necessary, you can then make design changes or install filters to achieve better machine performance.

A wide range of automatic configuration assistants make it easy to set up your new servo systems correctly, even for less experienced users.

Meeting global norms and standards

Mitsubishi Electric's MR-E Super servo amplifiers and motors meet all the standards and specifications laid down in the EU Low Voltage Directive 73/23/EEC and the Machinery Directive 98/37/EC. Needless to say that all systems carry the CE mark and are certified as conforming to UL, cUL.



Specifications ///

| Servo amplifier MR-E-A/AG ^① | 10A 10AG | 20A 20AG | 40A 40AG | 70A 70AG | 100A 100AG | 200A 200AG |
|--|--|----------------|----------------|---------------------------------|----------------|----------------|
| Performance | 0.1 kW | 0.2 kW | 0.4 kW | 0.75 kW | 1 kW | 2 kW |
| Power supply | 3phase 200 – 230 V AC, 50/60 Hz; 1phase 200 – 230 V AC, 50/60 Hz | | | 3phase 200 – 230 V AC, 50/60 Hz | | |
| Control system | Sinusoidal PWM control / current control system | | | | | |
| Dynamic brake | Built-in | | | | | |
| Protective functions | Overcurrent shutdown, regeneration overvoltage shutdown, overload shutdown (electronic thermal), encoder fault protection, regeneration fault protection, undervoltage / sudden power outage protection, overspeed protection, excess error protection | | | | | |
| Structure/protection | Self-cooling, open (IP00); 200A/AG fan-cooling, open (IP00) | | | | | |
| Environment | Ambient temperature: Operation: 0 – 55 °C (no freezing); Storage: -20 – 65 °C (no freezing) | | | | | |
| | Ambient humidity: Operation: 90 % RH max. (no condensation); Storage: 90 % RH max. (no condensation) | | | | | |
| | Others: Elevation: 1000 m or less above sea level; Oscillation: 5.9 m/s ² (0.6 G) max. | | | | | |
| Weight | kg | 0.7 | 0.7 | 1.1 | 1.7 | 2.0 |
| Dimensions (W x H x D) | mm | 50 x 168 x 135 | 50 x 168 x 135 | 70 x 168 x 135 | 70 x 168 x 190 | 90 x 168 x 195 |

① A type: pulse-train input interface, AG type: analog input interface

| Servo amplifier | MR-E-A | MR-E-AG |
|-----------------------|----------------------------|--|
| Position control mode | Max. input pulse frequency | 1 Mpps (differential receiver), 200 kpps (open collector) |
| | Positioning feedback pulse | 131072 pulses per servo motor rotation |
| | Torque limit | Set by parameters |
| Speed control mode | Control range | Internal speed command 1:5000 |
| | Fluctuation rate | ±0.01 % max. (load fluctuation 0 – 100 %) |
| | Torque limit | Set by parameters or external analog input (0 to ±10 V DC / max. torque) |
| Torque control mode | Command input | 0 to ±8 V DC / max. torque |
| | Speed limit | Set by parameters or external analog input (0 to ±10 V DC / rated speed) |

| Servo motor series | Speed [rpm] | Rated output capacity [kW] | Rated torque [Nm] | Type ^② | Feature | Amplifier assignment MR-E | | | | | |
|--------------------|---------------|----------------------------|-------------------|---------------------|---------------------------------|---------------------------|-------------|-------------|-------------|---------------|---------------|
| | | | | | | 10A 10AG | 20A 20AG | 40A 40AG | 70A 70AG | 100A 100AG | 200A 200AG |
| HF-KE | Rated: 3000 | 0.1 | 0.32 | HF-KE13(B)W1-S100 | Low inertia, small capacity | ● | | | | | |
| | | 0.2 | 0.64 | HF-KE23(B)KW1-S100 | | | ● | | | | |
| | Maximum: 4500 | 0.4 | 1.3 | HF-KE43(B)KW1-S100 | | | | ● | | | |
| | | 0.75 | 2.4 | HF-KE73(B)KW1-S100 | | | | | ● | | |
| HF-SE | Rated: 2000 | 0.5 | 2.39 | HF-SE52(B)KW1-S100 | Medium inertia, medium capacity | | | | ● | | |
| | | 1.0 | 4.77 | HF-SE102(B)KW1-S100 | | | | ● | | | |
| | Maximum: 3000 | 1.5 | 7.16 | HF-SE152(B)KW1-S100 | | | | | | ● | |
| | | 2.0 | 9.55 | HF-SE202(B)KW1-S100 | | | | | | | ● |

② Keyway shaft as standard (HF-KE motors come with key, HF-SE motors without) except for HF-KE13; (B) = with electromagnetic brake

EUROPEAN BRANCHES

| | |
|---|-----------------------|
| MITSUBISHI ELECTRIC EUROPE B.V. Gothaer Straße 8 D-40880 Ratingen Phone: +49 (0)2102 / 486-0 | GERMANY |
| MITSUBISHI ELECTRIC EUROPE B.V. Radlická 714/113a CZ-158 00 Praha 5 Phone: +420 (0)251 551 470 | CZECH REPUBLIC |
| MITSUBISHI ELECTRIC EUROPE B.V. 25, Boulevard des Bouvets F-92741 Nanterre Cedex Phone: +33 (0)1 / 55 68 55 68 | FRANCE |
| MITSUBISHI ELECTRIC EUROPE B.V. Viale Colleoni 7 I-20041 Agrate Brianza (MB) Phone: +39 039 / 60 53 1 | ITALY |
| MITSUBISHI ELECTRIC EUROPE B.V. Krakowska 50 PL-32-083 Balice Phone: +48 (0)12 / 630 47 00 | POLAND |
| MITSUBISHI ELECTRIC EUROPE B.V. Carrera de Rubi 76-80 E-08190 Sant Cugat del Vallés (Barcelona) Phone: 902 131121 // +34 935653131 | SPAIN |
| MITSUBISHI ELECTRIC EUROPE B.V. Travellers Lane UK-Hatfield, Herts. AL10 8XB Phone: +44 (0)1707 / 27 61 00 | UK |

EUROPEAN REPRESENTATIVES

| | | | | | | | | | | | | | |
|---|---------------------------|--|-----------------------|---|--------------------|--|-----------------|---|--------------------|--|---------------------|--|----------------|
| GEVA Wiener Straße 89 AT-2500 Baden Phone: +43 (0)2252 / 85 55 20 | AUSTRIA | AutoCont CS, s.r.o. Technologická 374/6 CZ-708 00 Ostrava-Pustkovec Phone: +420 595 691 150 | CZECH REPUBLIC | Kazpromautomatics Ltd. Mustafina Str. 7/2 KAZ-470046 Karaganda Phone: +7 7212 / 50 11 50 | KAZAKHSTAN | Beijer Electronics AS Postboks 487 NO-3002 Drammen Phone: +47 (0)32 / 24 30 00 | NORWAY | INEA d.o.o. Stegne 11 SI-1000 Ljubljana Phone: +386 (0)1 / 513 8100 | SLOVENIA | SHERF Motion Techn. Ltd. Rehov Hamerkava 19 IL-58851 Holon Phone: +972 (0)3 / 559 54 62 | ISRAEL | | |
| TEHNIKON Oktyabrskaya 16/5, Off. 703-711 BY-220030 Minsk Phone: +375 (0)17 / 210 46 26 | BELARUS | B.ELECTRIC, s.r.o. Mladoboleslavská 812 CZ-197 00 Praha 19 - Kbely Phone: +420 286 850 848 | CZECH REPUBLIC | Beijer Electronics SIA Viestenas iela 2 LV-1035 Riga Phone: +371 (0)784 / 2280 | LATVIA | Sirius Trading & Services Aleea Lacul Morii Nr. 3 RO-060841 Bucuresti, Sector 6 Phone: +40 (0)21 / 430 40 06 | ROMANIA | Beijer Electronics AB Box 426 SE-20124 Malmö Phone: +46 (0)40 / 35 86 00 | SWEDEN | CEG INTERNATIONAL Cebaco Center/Block A Autostrade DORA Lebanon - Beirut Phone: +961 (0)1 / 240 430 | LEBANON | | |
| ESCO D & A Culliganlaan 3 BE-1831 Diegem Phone: +32 (0)2 / 717 64 30 | BELGIUM | Beijer Electronics UAB Lykkęgardšvejs 17, 1. DK-4000 Roskilde Phone: +45 (0)46 / 75 76 66 | DENMARK | Beijer Electronics UAB Savanoriu Pr. 187 LT-02300 Vilnius Phone: +370 (0)5 / 232 3101 | LITHUANIA | Craft Con. & Engineering d.o.o. Bulevar Svetog Cara Konstantina 80-86 SER-18106 Nis Phone: +381 (0)18 / 292-24-45 | SERBIA | Econote AG Hinterdorfstr. 12 CH-8309 Nürensdorf Phone: +41 (0)44 / 838 48 11 | SWITZERLAND | CBI Ltd. Private Bag 2016 ZA-1600 Isando Phone: +27 (0)11 / 928 2000 | SOUTH AFRICA | | |
| Koning & Hartman b.v. Woluwelaan 31 BE-1800 Vilvoorde Phone: +32 (0)2 / 257 02 40 | BELGIUM | Beijer Electronics OÜ Pärnu mnt.160i EE-11317 Tallinn Phone: +372 (0)6 / 51 81 40 | ESTONIA | ALFATRADE Ltd. 99, Paola Hill Malta- Paola PLA 1702 Phone: +356 (0)21 / 697 816 | MALTA | INEA SR d.o.o. Izletnicka 10 SER-113000 Smederevo Phone: +381 (0)26 / 617 163 | SERBIA | GTS Bayraktar Bulvarı Nutuk Sok. No:5 TR-34775 Yukari ISTANBUL Phone: +90 (0)216 526 39 90 | TURKEY | AutoCont Control s.r.o. Radlinského 47 SK-02601 Dolny Kubin Phone: +421 (0)43 / 5868210 | SLOVAKIA | CSC Automation Ltd. 4-B, M. Raskovoyi St. UA-02660 Kiev Phone: +380 (0)44 / 494 33 55 | UKRAINE |
| INEA BH d.o.o. Aleja Lipa 56 BA-71000 Sarajevo Phone: +387 (0)33 / 921 164 | BOSNIA AND HERZEG. | ITECO A.B.E.E. 5, Mavrogenous Str. GR-18542 Piraeus Phone: +30 211 / 1206 900 | GREECE | INTEHSIS srl bld. Traian 23/1 MD-2060 Kishinev Phone: +373 (0)22 / 66 4242 | MOLDOVA | CS MTrade Slovensko, s.r.o. Vajanského 58 SK-92101 Piestany Phone: +421 (0)33 / 7742 760 | SLOVAKIA | | | | | | |
| AKHNATON 4 Andrej Ljapchev Blvd. Ph 21 BG-1756 Sofia Phone: +359 (0)2 / 817 6004 | BULGARIA | MELTRADE Ltd. Fertő utca 14. HU-1107 Budapest Phone: +36 (0)1 / 431-9726 | HUNGARY | Koning & Hartman b.v. Haarlerbergweg 21-23 NL-1101 CH Amsterdam Phone: +31 (0)20 / 587 76 00 | NETHERLANDS | | | | | | | | |



Mitsubishi Electric Europe B.V. /// FA - European Business Group /// Gothaer Straße 8 /// D-40880 Ratingen /// Germany
Tel.: +49(0)2102-4860 /// Fax: +49(0)2102-4861 120 /// info@mitsubishi-automation.com /// www.mitsubishi-automation.com

Specifications subject to change /// Art. no. 218276-A /// 10.2008

All trademarks and copyrights acknowledged.